

## KARAKTERISTIK & SPESIFIKASI KINERJA

No	TYPE	KARAKTERISTIK	SPESIFIKASI KINERJA	ANALISA RESIKO ALAT	SPESIFIKASI KEMASAN
1	3012 D4-ST	Sistem pengoperasian adjustable hi-low, foot raise dilakukan secara manual dengan cyliner dan back raise dilakukan secara manual dengan menggunakan Cylinder	Pengoperasian secara manual diputar	Cara penggunaan yang salah dan seringnya diputar crank akan cepat rusak	CB/F K200/M150x3/K200 975 x 2350 x 170
		Sistem penguncian roda caster menggunakan sistem penguncian ganda ( double lock caster)	Fungsi lock pada caster akan maksimal jika posisi bed diletakkan pada lantai datar	Posisi penempatan bed harus dalam kondisi permukaan lantai datar, karena bila diletakkan posisi miring maka fungsi lock pada akan caster akan cepat rusak	

### CB 3012 D4-ST



#### OPERATION SYSTEM

A unique eye catching foldable crank is designed to give high-low bed adjustment.



Crank operation system

Back raise adjustment

#### CASTER OPERATION SYSTEM

Independent lock caster (one at front and one at back of the bed) provides stability and secure parking.

